



**Product:** [5500UE](#) 

Security & Sound, 2 Conductor 22 AWG, BC, CMR

## Product Description

Security & Commercial Audio Cable, Riser-CMR, 2-22 AWG stranded bare copper conductors with polypropylene insulation, PVC jacket with ripcord

## Technical Specifications

### Product Overview

Suitable Applications:	Security Systems, Intercom/PA Systems, Sound/Audio Systems, Power Limited Controls, Single Line Telephone
------------------------	---

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	22 AWG	7x30	BC - Bare Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PP - Polypropylene	0.008 in (0.20 mm)	0.045 in (1.1 mm)	Black, Red

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.123 in (3.12 mm)	Yes

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Inductance	Max. Current
Conductor(s)	16.9 Ohm/1000ft (55.4 Ohm/km)	17 pF/ft (56 pF/m)	0.17 $\mu$ H/ft (0.56 $\mu$ H/m)	6 Amps per Conductor at 25°C

#### Voltage

UL Voltage Rating
300 V

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

#### Bend Radius

Stationary Min.	Installation Min.
1.2 in (30 mm)	1.2 in (30 mm)

Max. Pull Tension:	18 lbs (8.2 kg)
Bulk Cable Weight:	8 lbs/1000ft (12 kg/km)

### Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Riser, IEEE 1202 FT4, IEC 60332-1-2

CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6500UH

## History

Update and Revision:	Revision Number: 0.659 Revision Date: 02-20-2026
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC/EAN
5500UE.00152	Chrome	Reel	152 m	8719605008596
5500UE.00305	Chrome	Reel	305 m	8719605008602
5500UE.K0305	Chrome	Reel	305 m	8719605008619
5500UE 008500	Gray	Reel	500 ft	612825162896
5500UE 008U500	Gray	UnReel	500 ft	612825420033
5500UE 0081000	Gray	Reel	1,000 ft	612825162919
5500UE 008U1000	Gray	UnReel	1,000 ft	612825162902
5500UE 008Z1000	Gray	ReelTuff Box	1,000 ft	612825163145
5500UE 005Z1000	Green	ReelTuff Box	1,000 ft	612825337171
5500UE 005U1000	Green, Dark	UnReel	1,000 ft	612825420026

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.