



Product: [9892](#) 

Transceiver 10BASE5, #20-4pr, FPO, PVC Jkt, CM

Product Description

IEEE 802.3 Ethernet Transceiver 10BASE5, 20 AWG stranded (7x28) tinned copper conductors, Datalene® insulation, 4 twisted pairs, overall polyester isolation tape + a tinned copper braid shield (95% coverage), drain wire, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	IEEE 802.3 Transceiver Cable
------------------------	------------------------------

Construction Details

Conductor

Element	Size	Stranding	Material	No. of Pairs
Pair(s)	20	7x28	TC - Tinned Copper	4

Insulation

Material	Nom. Insulation Diameter	Color Code	Notes
PE - Polyethylene (Foam)	0.077 in (2.0 mm)	Gray & White, Yellow & Orange, Blue & Green, Black & Red	HDPE

Inner Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Braid	Tinned Copper (TC)	95%	22 AWG (7x30) TC

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.398 in (10.1 mm)

Electrical Characteristics

Electricals

Nom. Characteristic Impedance
78 Ohm

Delay

Max. Delay Skew	Nom. Velocity of Prop.
78 ns/100m	78%

High Frequency

Max. Insertion Loss (Attenuation)
6 dB/100m

Voltage

UL Voltage Rating

30 V (AWM 2919), 300 V (CL2)

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-40°C To +80°C

Bend Radius

Stationary Min.	Installation Min.
3.98 in (101 mm)	3.98 in (101 mm)

Max. Pull Tension:	175 lbs (79.4 kg)
Bulk Cable Weight:	93 lbs/1000ft

Standards and Compliance

Flammability / Reaction to Fire:	UL1685 UL Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 800, CL2, CM
AWM Compliance:	AWM 2919
CEC / C(UL) Compliance:	CM
IEEE Compliance:	IEEE 802.3
European Directive Compliance:	EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	DEC Part No. 17-01320-00
Plenum Number:	89901

History

Update and Revision:	Revision Number: 0.477 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
9892 0061000	Blue, Light	612825260103	C
9892 006500	Blue, Light	612825260110	C
9892 0065000	Blue, Light	612825260127	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.