


**Product:** [9926](#)
**Lead Wire, #26 Str TC, PVC Ins, AWM 1007 AWM 1569**
[Request Sample](#)

## Product Description

Low Temp Plastic Lead Wire, 26AWG (7x34) Tinned Copper, PVC Insulation, AWM 1007 AWM 1569 CSA TYPE TR-64 TRSR-64

## Technical Specifications

### Product Overview

Suitable Applications: inter-connection circuits, internal wiring of computer and electronic equipments, internal wiring of appliances

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	26	7x34	TC - Tinned Copper

#### Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	0.016 in (0.41 mm)	0.051 in (1.3 mm)

Overall Cable Diameter (Nominal): 0.051 in (1.3 mm)

### Electrical Characteristics

#### Voltage

UL Voltage Rating
300 V RMS

### Mechanical Characteristics

#### Temperature

UL Temperature
105°C

#### Bend Radius

Stationary Min.	Installation Min.
0.21 in (5.3 mm)	0.21 in (5.3 mm)

Max. Pull Tension: 3.5 lbs (1.6 kg)

Bulk Cable Weight: 1.9 lbs/1000ft

### Standards and Compliance

Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	VW-1
AWM Compliance:	AWM 1007, AWM 1569
CEC / C(UL) Compliance:	TRSR-64
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

## History

Update and Revision:

Revision Number: 0.460 Revision Date: 09-07-2025

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9926 010100	Black	Reel	100 ft	612825263784	
9926 0101000	Black	Reel	1,000 ft	612825263791	P
9926 0131000	Blue, Dark	Reel	1,000 ft	612825349907	P
9926 0011000	Brown	Reel	1,000 ft	612825263708	P
9926 0081000	Gray	Reel	1,000 ft	612825263760	P
9926 0051000	Green, Dark	Reel	1,000 ft	612825349891	P
9926 0031000	Orange	Reel	1,000 ft	612825263739	P
9926 002100	Red	Reel	100 ft	612825263715	
9926 0021000	Red	Reel	1,000 ft	612825263722	P
9926 0071000	Violet	Reel	1,000 ft	612825263753	P
9926 0091000	White	Reel	1,000 ft	612825263777	P
9926 0041000	Yellow	Reel	1,000 ft	612825263746	P

Footnote:

P - STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M= FOR 1 OR 2 STRIPES. 10,000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL, WITH A MINIMUM LENGTH OF 100'.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.