

Product: [FD4D096LK](#)

Indoor/Outdoor Riser OM4 Distribution 96Fibers
Product Description

FX Indoor/Outdoor OM4 Distribution Tight Buffer 96 Fibers LSZH Sub-Units (12F) Black Jacket

Technical Specifications
Product Overview

Product Category:	Fiber Distribution Cable
Suitable Applications:	Premise Backbone

Fiber Specifications

Fiber Type:	OM4
Fiber Core Diameter:	50/125 μm
Fiber Buffer Material:	LSZH - Low Smoke Zero Halogen
Fiber Buffer Diameter:	900 μm
Fiber Count:	96
Fiber Color Coding:	TIA-598-D

Cable Construction

Number of Active Subunits:	8
Fibers Per Subunit:	12
Subunit Diameter:	0.230 in (5.8 mm)
Subunit Color:	Erika Violet
Fiber SubUnit Strength Members:	Waterblocking aramid yarns
Central Strength Member Type:	Upjacketed GRP
Core Wrap Material:	Waterblocking tape
Cable Core Water Blocking:	Waterblock Tape

Outer Jacket Specifications

Jacket Material:	LSZH - Low Smoke Zero Halogen (Flame Retardant)
Nom. Diameter:	0.977 in (24.8 mm)
Outer Jacket Color:	Black
Outer Jacket Ripcord:	1

Optical Characteristics

Wavelength	850 nm	1300 nm
Max. Attenuation	3.0 dB/km	1.0 dB/km
1 Gigabit Ethernet Performance	1100 m	550 m
10 Gigabit Ethernet Performance	550 m	--
Min. Effective Modal Bandwidth (EMB)	4700 MHz.km	--
Min. Overfilled Launch (OFL) Bandwidth	3500 MHz.km	500 MHz.km

Mechanical Characteristics

Minimum Bend Radius During Installation:	15x Cable OD
Minimum Bend Radius During Operation:	10x Cable OD

Max. Tensile Strength During Installation:	2670 N (600 lbf)
Max. Tensile Strength During Operation:	800 N (180 lbf)
Crush Resistance:	220 N/cm
Bulk Cable Weight:	343 lbs/kft (511 kg/km)

Temperature Range

Installation Temperature Range:	-10°C to +60°C
Operating Temperature Range:	-40°C to +70°C
Storage Temperature Range:	-40°C to +70°C

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Sunlight Resistance, Burial
Sustainability:	CA Prop 65, Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	OFNR, FT4
ICEA Compliance:	S-104-696
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16

History

Update and Revision:	Revision Number: 0.99 Revision Date: 09-07-2025
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	UPC
FD4D096LK	Black	Reel	612825380757

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.