

NB1810-L4E-G

Industrial Router with LTE + GbE + SFP + 4x GbE + GNSS

High-performance and modular mobile router with Gigabit Ethernet and SFP port for use in industrial environment.



Keyfeatures

Mobile / Cellular	1x LTE, UMTS, GSM
SIM	2x Micro SIM
Ethernet	4x Gigabit Ethernet (4-Port Switch), 1x SFP/Gigabit Ethernet Combo, 1x Gigabit Ethernet
Extended Storage	1x SD Card
Serial / Fieldbus	1x RS-232/485
Positioning	Multi-GNSS
Operation Temperature	-40 °C to +70 °C
Software	Routing, Network Services, VPN, Firewall, Link Management, Supervisor, SDK, free updates
Compliance	CE (RED)
Modularity	Extensions on request

Product description

The NB1810 is a powerful and robust cellular router designed for use in industrial environments.

Applications

- Condition Monitoring
- Industrial Security
- Factory Automation
- Remote Management
- Smart Buildings
- Point of Sale
- Smart Grid
- Oil & Gas
- Renewable Energy
- CCTV

Specifications

Mobile / Cellular	Standard	1x Multimode LTE, UMTS, GSM for EMEA 4G - LTE B1, B3, B7, B8, B20, B28A 3G - DC-HSPA+/UMTS B1 (2100), B3 (1800), B8 (900) 2G - GSM/GPRS/EDGE B3 (1800), B8 (900) Category LTE Cat 4 Antenna ports 2x2 MIMO Data rate down / up (max) 150 Mbps / 50 Mbps Voice CSFB, VoLTE (with optional Software License) FCC ID - Region Europe
	Region Connectors SIM	Europe 2x SMA female 2x Micro SIM - 3FF
Ethernet	Standard	1x Gigabit Ethernet Ethernet standard 1000BASE-T, Auto MDIX Speed 10/100/1000 Mbps 1x Gigabit Ethernet / SFP combo (software switchable) Ethernet standard 1000BASE-T, Auto MDIX SFP standard Depending on module Speed 10/100/1000 Mbps Combo port SFP or GbE interface activated (software switchable) 4x Gigabit Ethernet Ethernet standard 1000BASE-T, Auto MDIX Speed 10/100/1000 Mbps
	Connector	2x RJ45, 1x SFP cage (mini GBIC), 4x RJ45

Positioning	Standard	1x Multi-GNSS Receiver BeiDou, Galileo, GLONASS, GPS gpsOne Gen 9 Antennas Active or passive Tracking Sensitivity Up to -160 dBm Services Standalone CEP (Circular Error Probability) < 2m (CEP 50), (Open sky conditions, Horizontal)
	Connector	1x SMA female
USB	Standard	1x USB 2.0 Host
	Connector	1x Type A
Serial, Fieldbus	Protocol	1x RS-232/485 combo (software switchable) Protocol EIA-232 Signals TX, RX Signal level High > 5 VDC, low < -5 VDC Bit rate Up to 115 200 Bit/s Protocol EIA-485 Signals A, B Signal level Differential output voltage, loaded 1.5 VDC – 3.6 VDC Bit rate Up to 115 200 Bit/s Termination 120 Ω for RS-485 configurable by software
	Connector	1x Terminal block header 3.5 mm (screw locking)
Extended Storage		SD Card Slot type microSD Speed (read / write) 600 kByte / s Application Store user and logging data of SDK or LXC applications SD card not included
System	Core	1.3 GHz dual-core, 1 GB RAM, 4 GB flash
	Module Slots	2x miniPCIe (PCIe + USB), 2x Extension (USB)
Software	Features	NetModule Router Software (supported features depending on product variant) Package The standard software package includes an intuitive user interface, covering all modern routing protocols and enables efficient mass deployment. General Fail-safe update (FOTA), upgrade via USB, HTTP(S), (S)FTP or TFTP, remote CLI & WebGUI, RADIUS authentication, Simple Certificate Enrollment Protocol (SCEP), Hardware- und Software Watchdog Remote Management Manage and monitor devices with SNMP V1/V2/V3, Netmodule vendor MIB, telnet, SSH, or HTTP/HTTPS Cellular Networking Multi-SIM / eSIM support (optional license), multi-APN support, signal strength monitoring, dedicated bearers, CSFB/VoLTE calls (optional license) Wireless LAN Access Point, Client Mode, Mesh Point or Dual Modes (Mesh Access Point / Access Point - Client), WLAN Pseudo-Bridge Client Mode: Multiple Client SSID Profile, Encryption: Open, WEP, WPA1/2/3-Personal, WPA1/2/3-Enterprise. Fast Roaming: Fast BSS Transition (802.11r), PreAuthentication, Protected Management Frames (802.11w) AP Mode: Multi-SSIDs (up to 8) Encryption: Open WPA1/2/3-Personal, WPA1/2/3-Enterprise Fast Roaming: Fast BSS Transition (802.11r), PreAuthentication, DFS support Protected Management Frames (802.11w) Client Tracking, Band Steering, Hide SSID broadcasting, Isolate Clients, Accounting, Short guard Intervall Mesh Mode (802.11s): Encryption: None, SAE. Gateway announcements Link Management Link prioritization, link aggregation, load balancing, multipath-TCP, IP-passthrough, link supervision, Services DHCP Client/Server, DNS Caching Server, Email, SMS Service, NTP Client/Server, SNTP Server, DynDNS, SSH Server, SNMP Agent, HTTP/HTTPS/FTP Server, IPv6 for WAN, 802.1x over Ethernet, MQTT Broker Voice Gateway (SIP, Call Routing, Audio with optional license) Coovachilli Hotspot Routing Destination, policy, multipath, mobile-IP, OSPF, BGP, multicast, TCP-MSS clamping, bridging discovery protocols LLDP, CDP, SONMP, EDP, FDP, IRDP, VRRP, STP/RSTP, VRRP, VLAN, PPPoE, VXLAN VPN OpenVPN, IPsec (IKEv1 and IKEv2), PPTP, GRE, L2TP, CSD dial-in, Certificate revocation service Firewall Stateful firewall, connection tracking, NAT, NAPT, masquerading, bridge filtering, Address translation (based on SRC and DST ports) Encryption supporting password protected PKCS12 files, integrated random certificate key generator, "Let's encrypt" certificate, ECC (Certificates with Elliptic Cryptography) Quality of Service Diffserv, SFQ, HTB, Priority-based Queuing, Netflow (Softflow) Programmability SDK Troubleshooting Logging, Ping, Traceroute, Tcpdump, Speed-test
	Licenses	GNSS Enabled service GNSS location service Server with JSON-, NMEA stream
Power	Input Voltage	12, 24, 48 VDC Nominal voltages 12, 24, 48 VDC Absolute voltages 12 VDC to 48 VDC (-25 % / +10 %)
	Connector Consumption	1x Terminal block header 3.5 mm (screw locking) 15 W (average), 22 W (max)
Mounting		DIN-Rail

Dimensions	W x H x D	Width 95 mm x height 128/140 mm x depth 121 mm
Weight		950 g
Environment	Operating Temperature Ingress Protection Level	-40°C to +70°C IP40
MTBF		220'000 h / 25.1 years, according SN29500 at environmental temperature 40 °C
Scope of delivery		Device, General safety instructions, Terminal block
Certifications	Compliance Domain	CE according to 2014/53/EU (RED), 2011/65/EU (RoHS) Industrial
Order Code		NB1810-L4E-G