


Product: [REVConnect WM Hor. Channel Kit](#) 



RVUHOCK-REVConnect Wall-Mount Horizontal Channel Kit

Product Description

The REVConnect Wall-Mount Horizontal Channel Kit comes with 2 components per kit

Technical Specifications

Product Overview

Suitable Applications:	IBDN System 4800,3600,2400,1200,10GX
------------------------	--------------------------------------

Physical Characteristics (Overall)

Overall Height:	4.575 in
Overall Width:	8.229 in
Overall Depth:	9.241 in
Packaging:	Packaged in a cardboard box
Weight:	1.6 lbs

Connectors

Materials

Description	Material	Color
Module	Aluminum	Silver

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C

Standards

UL Rating:	UL1863
------------	--------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes

Flammability, LSOH, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Related Part Numbers

Related Parts:	REVConnect wall termination kit, REVConnect wall connector mount, REVConnect wall cable dressing module, REVConnect cable management channel, REVConnect wall horizontal channel kit
----------------	--

Variants

Item #	Color	UPC
RVUHOCK	Silver	611589237963

Product Notes

Included Parts:	8 grommets; 8 plungers; 1 installation guide
Notes:	Refer to Installation Guide PX106711 (English) or visit our web site at http://www.belden.com

History

Update and Revision:	Revision Number: 0.232 Revision Date: 02-03-2025
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.