

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	10[mm]
Max. Air Flow:	5.6[CFM]
Max. Air Flow:	0.16[m ³ per min]
Max. Static Pressure:	0.15[In H ₂ O]
Max. Static Pressure:	37[Pa]
Fan Speed:	6500[RPM]
Noise:	24[dB]
Life Expectancy:	40 degree C 30,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	5[V]
Operating Voltage - Lower:	4.5[V]
Operating Voltage - Upper:	5.5[V]
Current:	0.13[A]
Input Power:	0.7[W]
Mass:	16[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	Active

DC Axial Fans