

### Detailed Specifications

|                          |                               |
|--------------------------|-------------------------------|
| Frame Width:             | 20[mm]                        |
| Frame Height:            | 45[mm]                        |
| Frame Depth:             | 45[mm]                        |
| Nominal Voltage:         | 12[V]                         |
| Max. Air Flow:           | 4.2[CFM]                      |
| Max. Static Pressure:    | 0.4[In H2O]                   |
| Speed:                   | 6000[min-1]                   |
| Noise:                   | 27[dB]                        |
| Life Expectancy:         | 25 degree C 50,000 Hours[L10] |
| Bearing Type:            | Sleeve Bearing                |
| Operating Voltage Lower: | 6[V]                          |
| Operating Voltage Upper: | 13.8[V]                       |
| Nominal Current:         | 0.09[A]                       |
| Input Power:             | 1.08[W]                       |
| Mass:                    | 25[g]                         |
| Status:                  | Active                        |