

Detailed Specifications

Frame Width:	50[mm]
Frame Height:	50[mm]
Frame Depth:	15[mm]
Max. Air Flow:	9.9[CFM]
Max. Air Flow:	0.28[m3 per min]
Max. Static Pressure:	0.1[In H2O]
Max. Static Pressure:	25[Pa]
Fan Speed:	4550[RPM]
Noise:	25[dB]
Life Expectancy:	40 degree C 40,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.06[A]
Input Power:	0.7[W]
Mass:	25[g]
Tach / Locked Rotor Output:	No
Status:	Active

DC Axial Fans