

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	25[mm]
Max. Air Flow:	39.2[CFM]
Max. Air Flow:	1.11[m ³ per min]
Max. Static Pressure:	0.98[In H ₂ O]
Max. Static Pressure:	244[Pa]
Fan Speed:	9200[RPM]
Noise:	54[dB]
Life Expectancy:	60 degree C 40,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	10[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.27[A]
Input Power:	6.5[W]
Mass:	90[g]
IP Rating:	IP68/IP69K
Tach / Locked Rotor Output:	No
Status:	Active