

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	38[mm]
Max. Air Flow:	50.15[CFM]
Max. Air Flow:	1.43[m ³ per min]
Max. Static Pressure:	2.31[In H ₂ O]
Max. Static Pressure:	575[Pa]
Fan Speed:	13000[RPM]
Noise:	58[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	10.8[V]
Operating Voltage - Upper:	13.2[V]
Current:	0.78[A]
Input Power:	9.4[W]
Mass:	123[g]
Tach / Locked Rotor Output:	No
Status:	Active