

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	38[mm]
Max. Air Flow:	73.1[CFM]
Max. Air Flow:	2.07[m3 per min]
Max. Static Pressure:	3.55[In H2O]
Max. Static Pressure:	887[Pa]
Fan Speed:	17000[RPM]
Noise:	66.5[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	8[V]
Operating Voltage - Upper:	13.2[V]
Current:	2.3[A]
Input Power:	27.6[W]
Mass:	125[g]
Tach / Locked Rotor Output:	No
Status:	Active