

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	20[mm]
Max. Air Flow:	27.5[CFM]
Max. Air Flow:	0.78[m3 per min]
Max. Static Pressure:	0.11[In H2O]
Max. Static Pressure:	28.3[Pa]
Fan Speed:	2600[RPM]
Noise:	27[dB]
Life Expectancy:	60 degree C 40,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.05[A]
Input Power:	0.6[W]
Mass:	80[g]
Tach / Locked Rotor Output:	Tach Output
Status:	Active

DC Axial Fans