

## Detailed Specifications

|                                    |                               |
|------------------------------------|-------------------------------|
| <b>Frame Width:</b>                | 80[mm]                        |
| <b>Frame Height:</b>               | 80[mm]                        |
| <b>Frame Depth:</b>                | 25[mm]                        |
| <b>Max. Air Flow:</b>              | 41.3[CFM]                     |
| <b>Max. Air Flow:</b>              | 1.17[m <sup>3</sup> per min]  |
| <b>Max. Static Pressure:</b>       | 0.15[In H <sub>2</sub> O]     |
| <b>Max. Static Pressure:</b>       | 37.5[Pa]                      |
| <b>Fan Speed:</b>                  | 3100[RPM]                     |
| <b>Noise:</b>                      | 30[dB]                        |
| <b>Life Expectancy:</b>            | 40 degree C 50,000 Hours[L10] |
| <b>Bearing Type:</b>               | Sleeve Bearing                |
| <b>Nominal Voltage:</b>            | 12[V]                         |
| <b>Operating Voltage - Lower:</b>  | 6[V]                          |
| <b>Operating Voltage - Upper:</b>  | 13.8[V]                       |
| <b>Current:</b>                    | 0.16[A]                       |
| <b>Input Power:</b>                | 1.9[W]                        |
| <b>Mass:</b>                       | 80[g]                         |
| <b>Tach / Locked Rotor Output:</b> | Tach Output                   |
| <b>Status:</b>                     | Active                        |