

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	38[mm]
Max. Air Flow:	141.2[CFM]
Max. Air Flow:	4[m3 per min]
Max. Static Pressure:	1.04[In H2O]
Max. Static Pressure:	260[Pa]
Fan Speed:	6700[RPM]
Noise:	61[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	14[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.92[A]
Input Power:	22.1[W]
Mass:	230[g]
Tach / Locked Rotor Output:	No
Status:	PCN

DC Axial Fans