

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	38[mm]
Nominal Voltage:	115[V]
Frequency:	60[Hz]
Max. Air Flow:	67[CFM]
Max. Air Flow:	1.9[m3 per min]
Max. Static Pressure:	0.1[In H2O]
Max. Static Pressure:	24.5[Pa]
Fan Speed:	1950[RPM]
Noise:	30[dB]
Life Expectancy:	25deg.C 100,000 hours[L10]
Bearing Type:	Ball Bearing
Ingress Protection:	none
Starting Voltage:	75[V]
Input Power (+10% - 20%):	7[V]
Current:	0.1[A]
Mass:	550[g]