

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	38[mm]
Nominal Voltage:	230[V]
Frequency:	50[Hz]
Max. Air Flow:	45.9[CFM]
Max. Air Flow:	1.3[m3 per min]
Max. Static Pressure:	0.06[In H2O]
Max. Static Pressure:	14.7[Pa]
Fan Speed:	1350[RPM]
Noise:	27[dB]
Life Expectancy:	25deg.C 100,000 hours[L10]
Bearing Type:	Ball Bearing
Ingress Protection:	none
Starting Voltage:	175[V]
Input Power (+10% - 20%):	6.5[V]
Current:	0.05[A]
Mass:	550[g]