

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	25[mm]
Max. Air Flow:	19[CFM]
Max. Air Flow:	0.54[m3 per min]
Max. Static Pressure:	0.16[In H2O]
Max. Static Pressure:	40.2[Pa]
Fan Speed:	4000[RPM]
Noise:	31[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	12[A]
Input Power:	1.4[W]
Mass:	65[g]
Tach / Locked Rotor Output:	Tach Output
Status:	EOL