

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	32[mm]
Max. Air Flow:	47.3[CFM]
Max. Air Flow:	1.34[m3 per min]
Max. Static Pressure:	0.16[In H2O]
Max. Static Pressure:	41[Pa]
Fan Speed:	2600[RPM]
Noise:	34[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	15[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.1[A]
Input Power:	2.4[W]
Mass:	230[g]
Tach / Locked Rotor Output:	No
Status:	Active

DC Axial Fans