

Detailed Specifications

Frame Size:	280[mm]
Frame Depth:	129[mm]
Nominal Voltage:	48[V]
Max. Air Flow:	1131[CFM]
Max. Static Pressure:	1.7[In H2O]
Speed:	2000[rpm]
Noise:	75[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Operating Voltage - Lower:	36[V]
Operating Voltage - Upper:	72[V]
Nominal Current:	3.4[A]
Input Power:	163.2[W]
Mass:	2100[g]