




APPROVED: _____
 DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	12/15/17	



SECTION A-A



SECTION B-B



SECTION C-C

SPECIFICATIONS:

Material: Phosphor Bronze

Plating: Tin Plated

Thickness: 0.15mm

Applicable Wire: AWG#26~#30

Electrical:

Voltage Rating: 150V AC,DC

Current Rating: 1A AC,DC

Contact Resistance: 20 mohms max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute
 -25°C to +85°C

Environmental:

Lead free, RoHS compliant.

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X $\pm .10$ ϕ .X $\pm .10$
 .XX $\pm .020$ ϕ .XX $\pm .015$
 .XXX $\pm .015$ ϕ .XXX $\pm .010$

APPROVALS		DATE
DRAWN	AY	12/15/17
CHECKED	MY	12/15/17
APPROVED		

ADAM TECH
 INTERCONNECTS
 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE 1.25MM TERMINAL FOR 125CHD-XX			
SIZE X	PART NO. 125CTDC-R	REV. -	
REF: S00124T	SCALE: NTS	SHEET 1 OF 1	