



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	9870	RELEASED	11/19/09	
A		UPDATE DRAWING	12/4/18	AY/IL


D




C



B



RECOMMENDED PCB LAYOUT

**SPECIFICATIONS:****Material:**

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Beige

Contacts: Copper Alloy

Plating:

Tin over Nickel underplate overall

Electrical:

Voltage rating: 125V AC, DC

Current rating: 1A AC, DC

A Contact resistance: 20 mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 15

A = .049 [1.25] X No. of Spaces

B = .049 [1.25] X No. of Spaces + .118 [3.00]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 ØX ± .10
 .XX ± .020 ØXX ± .015
 .XXX ± .015 ØXXX ± .010

APPROVALS	DATE
DRAWN	DY
CHECKED	
APPROVED	

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE		
.049 [1.25] PITCH WIRE TO BOARD HEADER RIGHT ANGLE TYPE		
SIZE	PART NO.	REV.
X	125SH-B-XX-TR	A
REF: S00123T	SCALE: NTS	SHEET 1 OF 1