





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		UPDATED SPECIFICATIONS	7/28/09	
B		REVISED SHAPE	3/23/11	
C		UPDATE DRAWING	1/19/19	AY/TY



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Electrical:

Current rating: 1A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant. 

Positions: 02 thru 15

A = .059 [1.50] X No. of Spaces.

B = .059 [1.50] X No. of Spaces + .118 [3.00].

C = .059 [1.50] X No. of Spaces + .075 [1.90].

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	BW	01/17/07
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
ZH 1.50mm HOUSING			
SIZE X	PART NO. 15CH-A-XX	REV. B	
REF: S00124T	SCALE: NTS	SHEET 1 OF 1	