

6

5

4

3






2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: Phosphor Bronze

Contact: Phosphor Bronze

Plating: Tin over Copper underplate overall

Electrical: Operating voltage: 50 VAC max

Current rating: 1 Amp max

Insulation resistance: 500 Mohms min @ 500 VDC

Dielectric withstanding voltage: 500 VAC for 1 minute

Contact resistance: 20 mohms max.

Mechanical: Recommended Wire Awg: 28 - 32 Awg

Temperature Rating: Operating temperature: -25°C to +85°C

Environmental: Lead free, RoHS compliant

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

SH1.0mm TERMINAL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED	
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010
APPROVALS	DATE
DRAWN BW	01/17/07
CHECKED	
APPROVED	

TITLE SH1.0mm TERMINAL

SIZE PART NO. 10TA-R

REV. -

SCALE: NTS SHEET 1 OF 1

REF: 1

1

2

3

4

5

6