




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/13/06	
A		PART REVISION	4/19/06	
B		ADDED DIM.	3/18/15	AY/RT
C		UPDATE DRAWING	4/13/18	AY/MY

SPECIFICATIONS:
Material:
Insulator: Nylon 66, rated UL 94V-0
Insulator color: Natural
Electrical:
Rated Voltage: 250V AC/DC
Rated Current: 3A AC/DC
Contact Resistance: 20 mohms max.
Insulation resistance: 1,000 Mohms min.
Withstand voltage: 1000V AC for 1 minute.
Temperature Rating:
-25°C to +85°C
Environmental:
Lead free, RoHS compliant

Positions: 2 thru 20
A = .098 [2.50] x No. of Spaces
B = .098 [2.50] x No. of Positions + .091 [2.30]
C = .098 [2.50] x No. of Positions + .028 [0.70]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES			ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
.X ± .10	Ø.X ± .10				
.XX ± .020	Ø.XX ± .015				
.XXX ± .015	Ø.XXX ± .010				
APPROVALS		DATE	TITLE WIRE TO BOARD PITCH: 2.5MM CRIMP HOUSING STRAIGHT TYPE		
DRAWN	LFJ	4/13/06			
CHECKED			SIZE X	PART NO. 25CH-B-XX	REV. C
APPROVED			REF: S00124T	SCALE: NTS	SHEET 1 OF 1