


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/4/19	
A		UPDATE SPEC.	11/3/20	OW/EY



SPECIFICATIONS:
 Material:
 Insulator: Nylon66, UL 94V-0
 Insulator color: Beige
 Electrical:
 Voltage rating: 250 VAC/DC
 Current rating: 3 A AC/DC
 Contact resistance: 20 mohms max.
 Insulation resistance: 1,000 Mohms min.
 Dielectric withstanding voltage: 1,000V AC for 1 minute
 Temperature Rating:
 Temperature range: -25°C to +85°C
 Environmental:
 Lead free, RoHS compliant



Positions: 02 thru 16
 A = .098 [2.50] x No. of Spaces
 B = .098 [2.50] x No. of Spaces + .130 [3.30]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS DRAWN HR 1/4/19 CHECKED MY 1/4/19 APPROVED		TITLE .098 [2.50] SHROUDED CRIMP TERMINAL HOUSING	
SIZE X	PART NO. 25CH-E6-XX	REV. A	
REF: S00186T		SCALE: NTS	SHEET 1 OF 1