





APPROVED: _____
 DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	7/13/11	
B		UPDATE DRAWING	4/13/18	AY/MY



SECTION C-C



SECTION A-A



SECTION B-B

SPECIFICATIONS:

Material: Phosphor Bronze

Plating: Tin plated

Electrical:

Rated Voltage: 250V AC/DC

Rated Current: 3A AC/DC

Contact Resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min.

Withstand voltage: 1000V AC for 1 minute.

Mechanical:

Wire Range: 22-28 AWG.

Thickness: 0.2mm

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS Compliant



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	7/13/11
CHECKED	AH	7/13/11
APPROVED		

**ADAM
 TECH**
 INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE			
.098 [2.50] CRIMP TERMINAL			
SIZE	PART NO.	REV.	
X	25CTB-R	A	
REF: S00124T		SCALE: NTS	SHEET 1 OF 1