


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/4/19	



SPECIFICATIONS:
 Material:
 Phosphor Bronze
 Plating:
 Tin over Copper underplate overall
 Mechanical:
 Wire Range: AWG #22-28
 Insulation OD: 1.9mm max
 Packaging: 10,000 Pcs/Reel
 Environmental:
 Lead free, RoHS Compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 ØX ± .10 .XX ± .020 ØXX ± .015 .XXX ± .015 ØXXX ± .010		ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE		.098 [2.50] CRIMP TERMINAL	
DRAWN	AY	1/4/19			
CHECKED	MY	1/4/19			
APPROVED					
		TITLE			
		SIZE X		PART NO. 25CTE6-R	
		REF: S00186T		SCALE: NTS	
				SHEET 1 OF 1	