



APPROVED: _____
 DATE: _____ TITLE: _____




Rev	AWO #	Description	Date	Appr
-		RELEASED	12/17/09	
A		UPDATED 1 & B DIMENSIONS	1/15/15	
B		UPDATE DRAWING	6/7/18	AY/KC




RECOMMENDED PCB LAYOUT



2P



ASSEMBLY VIEW



Positions: 02 thru 20

A = .098 [2.50] x of Spaces

B = .098 [2.50] x of Spaces +.197 [5.00]

C = .098 [2.50] x of Spaces +.138 [3.50]

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Nature

Contacts: Brass, Tin plated

Electrical:

Voltage rating: 250V AC/DC

Current rating: 3A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710
APPROVALS DRAWN DY CHECKED APPROVED		DATE 12/17/09		TITLE .098 [2.50] SHROUDED HEADER, RIGHT ANGLE
SIZE X		PART NO. 25SH-B-XX-TR		REV. B
REF: S00124T		SCALE: NTS		SHEET 1 OF 1