





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/24/12	
A		UPDATE DRAWING	7/1/15	AY/RT
B		UPDATE DIM.	6/14/16	AY

D



C



B

SECTION A-A

Aseemble state

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Nature

Contact: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Rated Voltage: 250V AC/DC

Rated Current: 3A AC/DC

Contact Resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min.

Withstand voltage: 1000V AC for 1 minute.

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

Positions: 2 thru 20

A = .098 [2.50] x No. of Spaces

B = .098 [2.50] x No. of Spaces + .197 [5.00]

C = .098 [2.50] x No. of Spaces + .138 [3.50]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X $\pm .10$ $\varnothing X$ $\pm .10$
 .XX $\pm .020$ $\varnothing XX$ $\pm .015$
 .XXX $\pm .015$ $\varnothing XXX$ $\pm .010$

APPROVALS

DATE

DRAWN

AY

CHECKED

LW

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE: WIRE TO BOARD PITCH: 2.50MM

WAFER STRAIGHT TYPE W/ KINK & PEG

SIZE	PART NO.	REV.
X	25SH-B-XX-TS-P	B
	REF: S00124T	SCALE: NTS
		SHEET 1 OF 1

