

Rev	AWO #	Description	Date	Appr
-		RELEASED	04/19/05	

6

5

4



3

2



1

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold Flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp max

Contact resistance: 20 mohms max

Insulation resistance: 5000 Mohms min

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.

A = .079 [2.00] X No. of Spaces + .362 [9.20]
B = .079 [2.00] X No. of Spaces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

2.0mm BOX HEADER, VERTICAL

PCB, GOLD PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	HILES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010
APPROVALS	DATE

DRAWN	SS	04/19/05
CHECKED		
APPROVED		

SIZE	PART NO.	REV.
X	2BHR-XX-VUA	-
REF:	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1

