

6

5

4

3


2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/8/19	



SPECIFICATIONS:

Material:

Contact: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Mechanical:

Wire Range: AWG #24-#28

OD: .059 [1.50] Max

Packaging:

10,000 piece reel

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE	
DRAWN	LH	10/8/19	
CHECKED	JC	10/8/19	
APPROVED			

ADAM TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
CRIMP CONTACT FOR 2CH-B-XX			
SIZE	PART NO.	REV.	
X	2CTB-R	-	
REF: S00099T		SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1