

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/10	

APPROVED: _____

DATE: _____ TITLE: _____

D




D

C

C

B

B



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 250 AC/DC

Current rating: 3A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

Positions: 2 thru 15

A = .079 [2.00] x No. of Spaces

B = .079 [2.00] x No. of Spaces + .157 [4.00]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 ØX ± .10
 .XX ± .020 ØXX ± .015
 .XXX ± .015 ØXXX ± .010

APPROVALS

DATE

DRAWN AY 11/23/10

CHECKED AH 11/23/10

APPROVED _____

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .079 [2.00] SHROUDED HEADER

RIGHT ANGLE, PCB

SIZE X PART NO. 2SH-H-XX-TR

REV. -

REF: S00015T

SCALE: NTS

SHEET 1 OF 1

 ROHS
COMPLIANT