

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description




Date

Appr

-

RELEASED

11/27/18



SPECIFICATIONS:

Material:

Insulator: PA66+30%GF, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 7 Amp

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 500 VAC

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED
MM ANGLE
X.X ± 0.30 ± 3°
X.XX ± 0.25
X.XXX ± 0.10

APPROVALS

DATE

DRAWN

AY

11/27/18

CHECKED

AC

11/27/18

APPROVED

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

8+23P, AUTOMOBILE, PITCH 4.00, L1.3*17.5 PIN

SIZE

X

PART NO.

ADT-AMMC3903MACT002

REV.

-

REF:

S00111C

SCALE: NTS

SHEET 1 OF 1