





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/27/18	



P.C.B LAYOUT



SPECIFICATIONS:

Material:

Insulator: PA6T+30%GF, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Current rating: 3 Amp

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 500 VAC

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED
MM ANGLE
X.X ± 0.25 ± 3°
X.XX ± 0.20
X.XXX ± 0.10

APPROVALS		DATE
DRAWN	AY	11/27/18
CHECKED	AC	11/27/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

2.54 PITCH PIN HEADER, 1*6 PIN, RIGHT ANGLE

SIZE	PART NO.	REV.
X	ADT-AMP1151106S3BR149E2	-
REF:	S00111C	SCALE: NTS
SHEET 1 OF 1		