

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE / NON-RETURNABLE

Rev

AWO #

Description


Date

Appr

-

RELEASED

11/15/18



4	TISSUE TAPE	3M 9888T
3	CONNECTOR	IPEX FOR Ø1.13mm
2	CABLE	Ø1.13mm CABLE BLACK
1	PCB	FR-4
ITEM	PART NAME	MATERIAL

SPECIFICATION

ELECTICAL PROPERTIES

FREQUENCY RANGE: 824~960/1710~2170 MHz

VSWR: 2.0

IMPEDANCE: 50Ω

GAIN: 2dBi

PHYSICAL PROPERTIES

WIRE: OD1.13 CABLE BLACK

CONNECTOR: IPEX

PCB: FR4

TISSUE TAPE: 3M9888T

OPERATING TEMPERATURE: -40~+80

STORAGE TEMPERATURE: -45~+85

ENVIRONMENTAL:

LEAD FREE, ROHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTEDMM
X ± 0.25
X.X ± 0.15
X.XX ± 0.10**ADAM**
TECH
INTERCONNECTS909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

3G EMBEDDED ANTENNA

APPROVALS

DATE

DRAWN

AY

11/15/18

CHECKED

AC

11/15/18

APPROVED

SIZE

X

PART NO.

ANT-DK-3G0EM22-I0300

REV.

-

REF: S00291T

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1