







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/8/19	



RECOMMENDED PCB LAYOUT

ASJ-112-I-T/R	ASJ-112-J-T/R	ASJ-112-M-T/R	ASJ-112-A-T/R	ASJ-112-B-T/R	ASJ-112-D-T/R

PACKAGED ON TAPE & REEL

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Plating:

Gold flash over Nickel underplate overall

Electrical:

Voltage rating: 30 VDC.

Current rating: 0.5 Amp.

Contact resistance: 30 mohms max.

Insulation resistance: 100 Mohms min.

Dielectric withstanding voltage: 500 VAC

Temperature Rating:

Operating temperature: -20°C to +70°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	8/8/19
CHECKED	BC	8/8/19
APPROVED		

ADAM TECH
INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		
STEREO PHONE JACK, 3.5mm		
SIZE X	PART NO. ASJ-112-X-T/R	REV. -
REF: S00002C	SCALE: NTS	SHEET 1 OF 1