

APPROVED: _____


DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/19/22	
A		UPDATE DRAWING	11/20/23	LH/RC




.606 [15.40]
ADAM TECH
.378 [9.60]
ATHT-001

BACK



FRONT



- Crimps solid barrel contacts and D-sub contacts with RS-232 interface connectors.
- Ergonomic handle designed for low-effort operation.

SPECIFICATIONS:

Mechanical:

Wire range : 20-26 #AWG
DIN 0.5-0.14 mm²

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

DRAWN	JJ	10/19/22
CHECKED	RC	10/19/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
CRIMP TOOL, D-SUB CONNECTOR TERMINAL ,20 TO 26 AWG

SIZE X	PART NO. ATHT-001	REV. A
REF: S00304T	SCALE: NTS	SHEET 1 OF 1