


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/22	
A		UPDATE DRAWING	11/16/23	JJ/RC



Unit: mm

SPECIFICATIONS:

Mechanical:

Wire range : 16~24 #AWG
DIN 0.25-1.5 mm²

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

DRAWN	JJ	11/23/22
CHECKED	RC	11/23/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
CRIMP TOOL, NON-INSULATED/OPEN BARREL TERMINAL
16 TO 24 AWG

SIZE X	PART NO. ATHT-012	REV. A
-----------	----------------------	-----------

REF: - SCALE: NTS SHEET 1 OF 1