


6 5 4 3 2 1


APPROVED: _____
DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/13/15	
A		ADDED 16.4FT LENGTH	5/13/20	
B		ADDED 6.56FT LENGTH	10/8/20	OW/BL



ADAM P/N	L
CA-USB-AM/AM-3FT	36.024"±1.181" [915±30mm]
CA-USB-AM/AM-6FT	72.047"±1.969" [1830±50mm]
CA-USB-AM/AM-10FT	120.079"±1.969" [3050±50mm]
CA-USB-AM/AM-16.4FT	196.85"±2.0" [5000±50.8mm]
CA-USB-AM/AM-6.56FT	78.740"±1.969" [2000±50mm]



SPECIFICATIONS:
Connector:
P1=P2= USB Connector 2.0 A Type Plug, Insulator Color: White, Overmold Color: Black, 50P PVC
Cable:
UL2725, (1P+2C)+A+B, OD: .189" [4.8mm] (28/24), Jacket Color: Black
Electrical Test:
All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE CUSTOMER ASSEMBLY, USB 2.0 PLUG TYPE A TO USB 2.0 PLUG TYPE A		
DRAWN	HR	10/13/15	SIZE X	PART NO. CA-USB-AM/AM-XFT	REV. B
CHECKED	TW	10/13/15	REF: S00087T	SCALE: NTS	SHEET 1 OF 1
APPROVED					