

6

5

4

3

2

1

APPROVED: _____


DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE / NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/5/21	

P1

P2



ADAM P/N	DIM.A(MM)	DIM.A(IN)
CA-BNC-P-P-02-500L	500±2	19"
CA-BNC-P-P-02-600L	600±3.5	23"
CA-BNC-P-P-02-610L	610±3.5	24"
CA-BNC-P-P-02-750L	750±3.5	29"
CA-BNC-P-P-02-1000L	1000±5	39"
CA-BNC-P-P-02-1200L	1200±5	47"
CA-BNC-P-P-02-1500L	1500±3.5	59"
CA-BNC-P-P-02-2000L	2000±10	78"
CA-BNC-P-P-02-2800L	2800±10	110"

SPECIFICATIONS:**Connector:**

P1= BNC Plug, Straight, Overmold Color: Black PVC

P2= BNC Plug, Straight, Overmold Color: Black PVC

Cable:

RG-174 C/U, Jacket Color: Black PVC

Electrical:

Nominal Impedance: 50 ohms

Electrical Test:All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.**Environmental:**

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ±.10 Ø.X ±.10
.XX ±.020 Ø.XX ±.015
.XXX ±.015 Ø.XXX ±.010

APPROVALS		DATE
DRAWN	LH	1/5/21
CHECKED	RC	1/5/21
APPROVED		

ADAM
TECH

 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

 TITLE
 CUSTOM CABLE ASSEMBLY, BNC PLUG
 TO BNC PLUG WITH RG-174 CABLE

SIZE	PART NO.	REV.
X	CA-BNC-P-P-02-XXXL	-
REF: S00092T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1