

6

5

4

3

2


1

APPROVED: _____

DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE
NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/21/20	

**SPECIFICATIONS:****Connector:**

P1= I-PEX Connector

P2= I-PEX Connector

Cable:

1.37mm Coaxial Cable, Color: Black

Electrical:

Impedance: 50 ohms

Frequency range: DC-6 GHz

Electrical Test:All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.**Environmental:**

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		ADAM TECH		909 Rahway Avenue, Union, NJ 07083	
INCHES HOLES		INTERCONNECTS		Phone: 908-687-5000	
.X ± .10 Ø.X ± .10				Fax: 908-687-5710	
.XX ± .020 Ø.XX ± .015					
.XXX ± .015 Ø.XXX ± .010					
APPROVALS		DATE		TITLE	
DRAWN	LH	9/21/20		CUSTOM CABLE ASSEMBLY, IPEX PLUG TO IPEX PLUG WITH OD 1.37MM CABLE	
CHECKED	RC	9/21/20			
APPROVED					
SIZE X		PART NO. CA-DKCA1-200L1-I0I0		REV. -	
REF: S00291T		SCALE: NTS		SHEET 1 OF 1	