

6

5

4

3


2

1


APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	8/23/22	

Front View
Side A

P1

Heat shrink tube
OD.: .197" [5mm]
Color: Black

P2

Front View
Side B

PIN OUT

Side A

Side B

1 SIGNAL WIRE 1

Shield Shield

CA-FJFJ-XX001X

SPECIFICATIONS:

Connector:

P1&P2= FAKRA Jack Code See page2, Straight, 30u" Gold Plated
Overmold: Thermoplastic, rated UL 94V-0

Cable:

RG-174/U:26AWG, Coaxial+Braid, OD.: .106" [2.7mm] PVC, Jacket Color: Black

Electrical:

Impedance: 50ohm

Temperature Rating:

Operating temperature: -40°C to +105°C

Electrical Test:

All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.

Environmental:

Lead free, RoHS compliant



ADAM P/N	L+T	
CA-FJFJ-XX0011	39.370" ± 1.181"	1000 ± 30mm
CA-FJFJ-XX0012	78.740" ± 1.969"	2000 ± 50mm
CA-FJFJ-XX0015	196.850" ± 3.937"	5000 ± 100mm

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	±.10	Ø.X	±.10
.XX	±.020	Ø.XX	±.015
.XXX	±.015	Ø.XXX	±.010

DRAWN	LH	8/23/22
CHECKED	RC	8/23/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH
ADAM
TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710TITLE
CUSTOM CABLE ASSEMBLY, FAKRA JACK STRAIGHT
TO FAKRA JACK STRAIGHT, RG174, 26AWG

SIZE X	PART NO. CA-FJFJ-XX-001X	REV. -
REF: S00013T	SCALE: NTS	SHEET 1 OF 2

6

5

4

3

2

1

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description

Date








Appr








SEE SHT 1 OF 2 FOR REVISION

CA-FJFJ-XX001X

Fakra Jack

P1 Coding P2 Coding

Coding	A	B	C	D	E	F	G
Plug							
Color	Black	White	Blue	Bordeaux Violet	Green	Brown	Grey

Coding	H	I	K	L	M	N	Z
Plug							
Color	Violet	Beige	Curry	Carmin Red	Pastel Orange	Pastel Green	Water Blue

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

ADAM
TECH

 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

DRAWN

LH

8/23/22

CHECKED

RC

8/23/22

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

TITLE

 CUSTOM CABLE ASSEMBLY, FAKRA JACK STRAIGHT
 TO FAKRA JACK STRAIGHT, RG174, 26AWG

SIZE

X

PART NO.

CA-FJFJ-XX-001X

REV.

-

REF: S00013T

SCALE: NTS

SHEET 2 OF 2

6

5

4

3

2

1