


APPROVED: _____

DATE: _____ TITLE: _____



CA-FJFM-XX002X

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/12/22	

D







Z Code Jack



P1 CODE	
Z	Water Blue
N	Pastel Green
M	Pink Orange
L	Carmine
K	Curry
I	Yellow
H	Violet
G	Grey
F	Brown
E	Green
D	Purple
C	Blue
B	White
A	Black
Code	Color
Jack	

P2 CODE	
Z	Water Blue
N	Pastel Green
M	Pink Orange
L	Carmine
K	Curry
I	Yellow
H	Violet
G	Grey
F	Brown
E	Green
D	Purple
C	Blue
B	White
A	Black
Code	Color
Plug	



Z Code Plug

L±T

SPECIFICATIONS:**Connector:**P1= FAKRA Female Code See Chart, Straight, Brass Gold Plated Contacts
ADAM-P/N: RF55-61Z-Y-02-50P2= FAKRA Male Code See Chart, Straight, Brass Gold Plated Contacts
ADAM-P/N: RF55-62Z-Y-02-50**Electrical:**

Contact resistance: 30 mohms max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 500 VAC

Cable:

RG316U, Color: Brown

Electrical Test:All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.**Environmental:**

IP Rating: IPX7

Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN LH 10/12/22

CHECKED RC 10/12/22

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM-P/N	L±T
CA-FJFM-XX00203WP	11.811"±1.969" [300±50mm]
CA-FJFM-XX00206WP	23.622"±1.969" [600±50mm]
CA-FJFM-XX00210WP	39.370"±1.969" [1000±50mm]
CA-FJFM-XX00220WP	78.740"±1.969" [2000±50mm]
CA-FJFM-XX00230WP	118.110"±1.969" [3000±50mm]
CA-FJFM-XX00240WP	157.480"±1.969" [4000±50mm]
CA-FJFM-XX00250WP	196.850"±1.969" [5000±50mm]

TITLE		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
ADAM TECH			
CUSTOM CABLE ASSEMBLY, FAKRA FEMALE STRAIGHT TO FAKRA MALE STRAIGHT , RG316U, IPX7 RATED			
SIZE	PART NO.	REV.	
X	CA-FJFM-XX002XWP	-	
REF: S00288T		SCALE: NTS	SHEET 1 OF 1