




APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/24/25	

Front view
SIDE AFront view
SIDE B

PIN ASSIGNMENT	
SIDE A	SIDE B
1	BLUE
2	ORANGE
3	GREEN
4	BROWN
SHIELD	SHIELD

SPECIFICATIONS:**Connector:**

P1&P2=HSD Straight Jack, Type see chart, Insulator: PBT, Shell: Brass
Crimp contact: 6u" Gold plated

Cable:

26AWG*4C+AL+B, OD: .181" [4.6MM], Jacket:TPU, Color: Black
Electrical:

Insulation resistance: 1000 Mohms min

Return loss: 20 dB min (0-1 GHz)

Mechanical:

Center Contact Retention Force: 10N min

Environmental:

Thermal shock & Humidity & Vibration: USCAR-17

Temperature Rating:

Operating temperature: -40°C to +105°C

Electrical Test:All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.**Packing:**

Standard: Bag

Environmental:

Lead free, RoHS compliant



ADAM-P/N	L+T
CA-HS04XJ-HS04XJ-1M	39.370±1.181" [1000±30MM]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED
 INCHES .X .± .10 .ØX .± .10
 .XX .± .020 .ØXX .± .015
 .XXX .± .015 .ØXXX .± .010

DRAWN LH 11/24/25

CHECKED RC 11/24/25

APPROVED

CONFIDENTIAL AND PROPRIETARY
 © Adam Tech. All rights reserved. This document contains confidential and
 proprietary information belonging to Adam Tech. It is provided solely for design and
 reference purposes by authorized parties. Any reproduction, distribution, display, or
 disclosure to third parties, in whole or in part, without the prior written consent of
 Adam Tech, is strictly prohibited. Adam Tech retains all rights, including copyright,
 trademark, trade secret, and all other intellectual property rights worldwide.

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
adam-tech.com

TITLE: HSD FAKRA JACK STRAIGHT 4P TO HSD FAKRA
JACK STRAIGHT 4P, 26AWG CABLE, WTPA


SIZE X PART NO. CA-HS04XJ-HS04XJ-XM REV. -

REF: S00013T SCALE: NTS SHEET 1 OF 1

APPROVED: _____

DATE: _____ TITLE: _____

CA-HS04XJ-HS04XJ-XM



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES REV.
 $\pm .10$ $\pm .10$
 $\pm .020$ $\pm .015$
 $\pm .015$ $\pm .010$

DRAWN LH 11/24/25

CHECKED RC 11/24/25

APPROVED

**ADAM
TECH**

 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 adam-tech.com

 TITLE: HSD FAKRA JACK STRAIGHT 4P TO HSD FAKRA
 JACK STRAIGHT 4P, 26AWG CABLE

 SIZE PART NO. REV.
 X CA-HS04XJ-HS04XJ-XM -

REF: S00013T SCALE: NTS SHEET 2 OF 2

CONFIDENTIAL AND PROPRIETARY
 © Adam Tech. All rights reserved. This document contains confidential and
 proprietary information belonging to Adam Tech. It is provided solely for design and
 reference purposes by authorized parties. Any reproduction, distribution, display, or
 disclosure to third parties, in whole or in part, without the prior written consent of
 Adam Tech, is strictly prohibited. Adam Tech retains all rights, including copyright,
 trademark, trade secret, and all other intellectual property rights worldwide.