


6 5 4 3 2 1

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/25/21	



8	SC Small Plastic	PBT White
7	SC Outer Shell	PBT Blue
6	SC Tail Sleeve	PVC Blue
5	Fiber optic cable	Fiberglass Shuck PVC Yellow
4	FC Tail Sleeve	PVC Black
3	FC Outer Shell	Metallic plating Ni
2	Ceramic core	Ceramic White
1	CAP	PP White
No	Name	Material

SPECIFICATIONS:

Electrical:

Standards of IEC,EIA/TIA, Telcordia

Return loss: 40dB min

Insertion loss: 0.20dB max

Temperature Rating:

Operating temperature: -25°C to +70°C

Environmental:

Lead free, RoHS compliant.



SC drawing

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED		
MM		
1~10	±1.00	
11~30	±2.00	
31~50	±3.00	
51~200	±5.00	
>200	±7.00	

DRAWN	JJ	5/25/21
CHECKED	JL	5/25/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE CUSTOM ASSEMBLY, OPTICAL SC ADAPTOR, 1 PORTS , PLUG W/STRAIN RELIEF		
SIZE X	PART NO. CA #OPSN1PNNC1NSR-C1	REV. -
REF: S00005C	SCALE: NTS	SHEET 1 OF 1