

6		5		4		3		2		1																																										
APPROVED: _____						Rev	AWO #	Description	Date	Appr																																										
DATE: _____ TITLE: _____						-		RELEASED	10/13/15																																											
CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE																																																				
P1 #4 #5 #1 #9 L P2 #5 #2 #3 #9 #1 #4 PIN ASSIGNMENT <table><tr><td>P1</td><td></td><td>P2</td></tr><tr><td>1</td><td>RED</td><td>1</td></tr><tr><td>2</td><td>WHITE</td><td>2</td></tr><tr><td>3</td><td>GREEN</td><td>3</td></tr><tr><td>4</td><td>BLACK</td><td>4</td></tr><tr><td>5</td><td>BLUE</td><td>5</td></tr><tr><td>6</td><td>YELLOW</td><td>6</td></tr><tr><td>7</td><td></td><td>7</td></tr><tr><td>8</td><td>PURPLE</td><td>8</td></tr><tr><td>9</td><td>ORANGE</td><td>9</td></tr><tr><td>S</td><td>BRAID</td><td>S</td></tr></table> <table><tr><td>ADAM P/N</td><td>L</td></tr><tr><td>CA-USB3-AM/BM-3FT</td><td>36.024"±1.181" [915±30mm]</td></tr><tr><td>CA-USB3-AM/BM-6FT</td><td>72.047"±1.969" [1830±50mm]</td></tr><tr><td>CA-USB3-AM/BM-10FT</td><td>120.079"±1.969" [3050±50mm]</td></tr></table>												P1		P2	1	RED	1	2	WHITE	2	3	GREEN	3	4	BLACK	4	5	BLUE	5	6	YELLOW	6	7		7	8	PURPLE	8	9	ORANGE	9	S	BRAID	S	ADAM P/N	L	CA-USB3-AM/BM-3FT	36.024"±1.181" [915±30mm]	CA-USB3-AM/BM-6FT	72.047"±1.969" [1830±50mm]	CA-USB3-AM/BM-10FT	120.079"±1.969" [3050±50mm]
P1		P2																																																		
1	RED	1																																																		
2	WHITE	2																																																		
3	GREEN	3																																																		
4	BLACK	4																																																		
5	BLUE	5																																																		
6	YELLOW	6																																																		
7		7																																																		
8	PURPLE	8																																																		
9	ORANGE	9																																																		
S	BRAID	S																																																		
ADAM P/N	L																																																			
CA-USB3-AM/BM-3FT	36.024"±1.181" [915±30mm]																																																			
CA-USB3-AM/BM-6FT	72.047"±1.969" [1830±50mm]																																																			
CA-USB3-AM/BM-10FT	120.079"±1.969" [3050±50mm]																																																			

SPECIFICATIONS:

Connector:

P1= USB 3.0 Connector A type Plug, Gold Flash Plated,
Insulator Color: Blue, Overmold Color: Blue, 50P PVC

P2= USB 3.0 Connector B type Plug, Gold Flash Plated,
Insulator Color: Blue, Overmold Color: Blue, 50P PVC

Cable:

UL20276, (30#*1P+D+A+M)*2C+30#*1P+26#*2C+A+B,
OD: .189" [4.8mm], Jacket Color Blue

Electrical Test:

All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.

Environmental:

Lead free, RoHS compliant

RoHS

COMPLIANT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		
INCHES		HOLES
.X ± .10	Ø.X ± .10	
.XX ± .020	Ø.XX ± .015	
.XXX ± .015	Ø.XXX ± .010	
APPROVALS		DATE
DRAWN	HR	10/13/15
CHECKED	TW	10/13/15
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE

CUSTOM ASSEMBLY, USB 3.0 PLUG TYPE A
USB 3.0 PLUG TYPE B

SIZE

X

PART NO.

CA-USB3-AM/BM-XFT

REV.

-

REF: S00087T

SCALE: NTS

SHEET 1 OF 1