



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/31/06	
A		UPDATED POSITIONS	8/23/06	
B		ADD INSERTION DEPTH DIM.	4/01/08	
C		REVISED SHAPE	6/5/12	
D		UPDATED POSITIONS	6/18/13	
E		UPDATED POSITIONS	5/8/15	AY/KW



SPECIFICATIONS:
Material:
Insulator: PBT, Glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
Plating:
Gold flash over Nickel underplate on contact area,
Tin over Copper underplate on PCB tails
Electrical:
Current rating: 3 Amps max.
Contact resistance: 20 mohms max. initial
Insulation resistance: 5,000 Mohms min.
Dielectric withstanding voltage: 1000 VAC for 1 minute
Temperature Rating:
Operating temperature: -55°C to +85°C
Environmental:
Lead free, RoHS compliant

Positions: 06 thru 96
A = .100 [2.54] x No. of Spaces
B = A + .200 [5.08]
C = A + .360 [9.14]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES Holes
.X ± .10 ØXX ± .10
.XX ± .020 ØXX ± .015
.XXX ± .015 ØXXX ± .010
APPROVALS DATE

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

CARD EDGE CONNECTOR
VERTICAL, PCB
SIZE PART NO. CE-XX-U
SCALE: NTS
SHEET 1 OF 1

DRAWN	LFJ	3/31/06	SIZE	PART NO.	CE-XX-U	REV.
CHECKED			X			E
APPROVED			REF:	S00043T	SCALE: NTS	SHEET 1 OF 1