



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/1/22	
A		UPDATE SPEC.	11/30/22	WX/RC


Ⓐ Lock Nut




Ⓑ Washer






Ⓔ Sealing Nut



Ⓒ Body



Ⓓ Seal



SPECIFICATIONS:

Material:

Lock Nut: PA66, rated UL 94V-2

Body: PA66, rated UL 94V-2

Sealing Nut: PA66, rated UL 94V-2

Washer: Nitrile Butylene

Seal: Nitrile Butylene

Mechanical:

Cable Range O.D.: 2.5-4.5mm

Thread O.D. L2: 8mm

Thread Length L2: 7.5mm

Spanner Size A&E: 13/12mm

Nut Torque: 0.2Nm Max.

Environmental:

Waterproof: IP68

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN	WX	11/1/22
CHECKED	RC	11/1/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE: WATERPROOF CONNECTOR, M8, 1 HOLE,
 CABLE GLAND, WATERPROOF: IP68

SIZE X	PART NO. CG-P-M8-1.25	REV. A
REF: S00211C	SCALE: NTS	SHEET 1 OF 1