



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AMO#	Description	Date	Appr
-		RELEASED	6/2/08	



B

C

D

SPECIFICATIONS:

Material:

Insulator: PBT, 30% glass reinforced, rated UL 94V-0

Insulator color: Black

Coax Insulator: Teflon, color white

Contacts: Brass

Shell: Steel, Tin plated

Hardware: Brass, Nickel plated

Plating: Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 10 - 40 Amps max

Coax Impedance: 50 Ohms

Contact resistance: 10 mohms max

Insulation resistance: 5,000 Mohms min

Dielectric withstand voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +125°C

Environmental:

Lead free, RoHS compliant

B

C

D

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

B

C

D

A

APPROVALS		DATE	TITLE	
DRAWN	DY	6/12/08	D-SUB COAX PLUG, D5W5, SOLDER, MALE	
CHECKED			SIZE	PART NO.
APPROVED			X	D5W5-PD-1

ROHS
COMPLIANT

6

5

4

3

2

1